



Specifications:

| | |
|------------------------------|--|
| Dielectric Strength | 500 VAC (50/60Hz) for 1 minute |
| Insulation Resistance | 100MΩ Min. at 500 VDC |
| Contact Resistance | 30MΩ Max. (Between Terminals) 20MΩ Max. (Switch Part) |
| Mechanical | 0.4kg to 3.0kg (Insertion Force) 0.4kg to 3.0kg (Extraction Force) |
| Life Test | 5,000 cycles of insertion and extraction at a rate 25 to 30 cycles per minute |