

Fixings and PCB Mounts

Order code	Manufacturer code	Description
33-3665	n/a	PACK 25 10MM CIRCULAR SPACER (RC)
33-3650	n/a	PACK 25 3MM CIRCULAR SPACER (RC)
33-3655	n/a	PACK 25 5MM CIRCULAR SPACER (RC)
33-3660	n/a	PACK 25 8MM CIRCULAR SPACER (RC)
33-3636	n/a	PACK 25 7MM NYLON SPACERS (RC)
33-3638	n/a	PACK 25 9MM NYLON SPACERS (RC)
33-3640	n/a	PACK 25 12MM NYLON SPACERS (RC)
33-3630	n/a	PACK 25 2MM NYLON SPACERS
33-3632	n/a	PACK 25 4MM NYLON SPACERS (RC)
33-3634	n/a	PACK 25 6MM NYLON SPACERS (RC)

Fixings and PCB Mounts	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

QMF22
Component - Plastics

February 13, 1996

E I DUPONT DE NEMOURS & CO INC
DUPONT POLYMERS, ENGINEERING POLYMERS
NYLON RESINS PO BOX 80713, CHESTNUT RUN
PLAZA, WILMINGTON DE 19880

E41938 (M)
1A card()

Mil Deg	Col	Min Thk mm	UL94 Flame Class	Emc	RTI		H W	H A	H V	D T	D R	D S	C T
					Mech with hmp	Mech w/o hmp							
Polyamide, Type 66 nylon (PA66), designated "Zytel", furnished in the form of pellets.													
132F+, 133L+, 135F+	All	0.71	94V-2	125	65	65	4	0	0	0	0	0	0
		1.5	94V-2	125	75	85	3	0	0	0	0	0	0
		3.0	94V-2	125	75	85	2	0	0	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	0	0	0	0
→ 101(F2)+, 101F+, 101L+, E101L+, E101(F1)+	All	0.71	94V-2	125	65	65	4	0	0	0	0	0	0
		1.5	94V-2	125	75	85	3	0	0	0	0	0	0
		3.0	94V-2	125	75	85	2	0	0	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	0	0	0	0

Reports: August 30, 1968; December 2, 1992.

Replaces E41938A dated July 24, 1995.

324299147

H0017

Underwriters Laboratories Inc.®

(Cont on A001 card)

D11J0D05183