

Order code	Manufacturer code	Description
85-2281	GUT-6600 (OPT 01)	HANDY DIGITAL IC TESTER (RE)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

Digital IC Tester/Handy Digital IC Tester/FLASH Writer



CE

GUT-6000A (Digital IC Tester)

FEATURES

- * Loop Test
- * Auto-Search
- * Self-Diagnosis
- * Over-Load Protection
- * Measures 1800 Kinds Device
- * 54/74 Series TTL and High Speed CMOS
- * 4000 and 4500 Series CMOS
- * Test Socket : 28-Pin



CE

GUT-6600 (Handy Digital IC Tester)

FEATURES

- * Easy-Operating Tester, Particularly be Designed for the Digital IC
- * Supported Device: 74/40/45/41/44 Serial
- * Small, Portable, Light and Power-Saving, Usable With Battery
- * Average Search Time: 0.8 Second
- * Display: 16 Characters in 1 Line LCD
- * Test Pins: 14 ~ 24 Pins



CE

GUT-6001C (FLASH Writer)

FEATURES

- * Windows and XP Driver
- * Small, Portable, Light and Usable With Batteries
- * Two Types of High Efficient Work Mode: Stand-Along Mode, PC Based Mode
- * LCD Display: 16 x 2 Characters
- * Can Set Programming Flow Chart, Oltages, Pulse Width & Other Parameters
- * Powerful HEX/ASCII Memory and Fusemap, Test Library and Full Screen Edit
- * Support File Format Binary Code, Intel HEX & 80/86 HEX

SPECIFICATIONS

	GUT-6000A	GUT-6600
TEST RANGE	54/74 series TTL and high speed CMOS CMOS 40/45 RCA1800	TTL 54/74 CMOS 40/45 DRAM41/44
TEST VOLTAGE	5V	5V
TEST TIME	Average Search Time :0.8Sec	Average Search Time : 0.8Sec
DISPLAY	16Characters in 1 line LCD	16 Characters in 1 line LCD
POWER SOURCE	AC100V~240V±10%,50/60Hz	Battery
ACCESSORIES	Instruction manual × 1 Power cord × 1	Instruction manual × 1 1.5V(AA)Battery × 4
DIMENSIONS & WEIGHT	335(W) ×105(H) ×300(D)mm, Approx. 1.5kg	160(W) × 45(H) × 110(D)mm, Approx. 0.34kg
OPTION		DC 9V/500mA adaptor SOP adaptor

SPECIFICATIONS

	GUT-6001C
SUPPORTED DEVICES	EPROM 27C/LV64~27C/LV080 EEPROM 27C64~28C040 FLASH EPROM 29C/LC256~29C/LC040 29EE/LE/VE512~29EE/LE/VE020 28F/LF/VF256~28F/LF/VF040 29F010~29F040 29F001~29F0025 39SF/VF512~39SF/VF040 49BV/F512~49BV/F040 49BV/F/LV001~49BV/F/LV002
TEST SOCKET	40Pin ×2
DISPLAY	16 ×2 Characters
POWER SOURCE	DC 9V/500mA adaptor
ACCESSORIES	CD: Driver software & Manual ×1 DC 9V/500mA adaptor USB cable ×1
DIMENSIONS & WEIGHT	160(W) ×45(H) ×110(D)mm, Approx. 0.5kg

ORDERING INFORMATION

GUT-6000A Digital IC Tester
GUT-6600 Handy Digital IC Tester
GUT-6001C FLASH Writer

Option
GUT-6600
Opt. 01: DV 9V/500mA adaptor
Opt. 02: SOP adaptor