


**Fixings and PCB Mounts**

<b>Order code</b>	<b>Manufacturer code</b>	<b>Description</b>
33-3632	n/a	PACK 25 4MM NYLON SPACERS (RC)

Fixings and PCB Mounts	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

成型尺寸	公差
5mm以下	±0.2
5~20mm	±0.3
20~40mm	±0.4
40~60mm	±0.5
60~100mm	±0.8
100mm以上	±1.0

REVISIONS			
REV	DESCRIPTION	DATE	BY



PART NO.	A
3-2	2.0
3-2.5	2.5
3-3	3.0
3-3.3	3.3
3-3.5	3.5
3-4	4.0
3-4.5	4.5
3-5	5.0
3-5.5	5.5
3-6	6.0
3-6.35	6.35
3-7	7.0
3-7.5	7.5
3-8	8.0
3-9	9.0
3-9.5	9.5
3-10	10.0
3-10.5	10.5
3-11	11.0
3-12	12.0
3-13	13.0
3-13.6	13.6
3-14	14.0

PART NO.	A
3-14	14.0
3-15	15.0
3-15.5	15.5
3-16	16.0
3-16.5	16.5
3-16.8	16.8
3-17	17.0
3-17.5	17.5
3-18	18.0
3-19	19.0
3-20	20.0
3-21	21.0
3-22	22.0
3-23	23.0
3-24	24.0
3-25	25.0
3-26	26.0
3-27	27.0
3-28	28.0
3-29	29.0
3-30	30.0

QMFZ2 Component - Plastics  
 E I DUPONT DE NEMOURS & CO INC  
 ENGINEERING POLYMERS CHESTNUT RUN PLAZA PO BOX 80713 WILMINGTON DE 19880

Wednesday, September 15, 2004

E41938

Material Designation: 101(+)(f1), 101E(+)(f1), 101L(+)(f1), E101(+)(f1), E101L(f1), 132P(+)(f1), 135F(+)(f1)  
 Product Description: Polyamide 66 (PA66), designated "Zytel" furnished as pellets.

Color	Min. Thick. (mm)	Flame Class	HWI	HAI	RTI Elec	RTI Imp	RTI Str	IEC GWIT	IEC GWFI
ALL	0.71	V-2	4	0	130	75	85	725	960
	1.5	V-2	3	0	130	75	85	750	960
	3	V-2	2	0	130	75	85	800	960
	6	V-2	2	0	130	75	85	800	960

CTI: 0

HVTR: 0

D495: 6

IEC Ball Pressure (C):

Dielectric Strength (kV/mm): 13

Volume Resistance (10<sup>12</sup> Ohm-cm): 14

Environmental Stability (W):

ISO Tensile Strength (MPa):

ISO Flexural Strength (MPa):

ISO Heat Deflection (C):

ISO Tensile Impact (kJ/m<sup>2</sup>):

ISO Izod Impact (kJ/m<sup>2</sup>):

ISO Charpy Impact (kJ/m<sup>2</sup>):

- (+) Virgin and regrid up to 50% by weight inclusive, have the same basic material characteristics.  
 (f1) Suitable for outdoor use with respect to exposure to Ultraviolet Light, Water Exposure and Immersion in accordance with UL 746C.

NOTE (1) Material designations that are color pigmented may be followed by suffix letters and numbers. (2) Material designations may be prefixed by "ZYI" or "MIN" or "ZEN" or "DEL" or "CRA" or "RYN".

Report Date: 7/29/1996

Underwriters Laboratories Inc®

UL94 small-scale test data does not pertain to building materials, furnishings and related contents. UL 94 small-scale test data is intended solely for determining the flammability of plastic materials used in components and parts of end-product devices and appliances, where the acceptability of the combination is determined by UL.

**康揚企業股份有限公司**  
 KANG YANG HARDWARE ENTERPRISE CO., LTD.  
**東莞康揚塑膠五金電子廠**  
 DONG GUAN KANG YANG PLASTIC HARDWARE COMPANY  
**康哲電腦配件(吳江)有限公司**  
 KANG CHE COMPUTER COMPONENTS(WUJIANG) CO.,LTD.

TITLE	圓體間隔柱
MATERIAL	NYLON 66 UL94V-2
FINISH	
COLOR	NATURAL
UNLESS OTHERWISE SPECIFIED TOLERANCE	SEE ABOVE

產品規格圖面	
DATE	1997.07.21
DRAWN	AMY
CHECK	王子銘
APPROVED	張玉芬

PART NUMBER	SEE ABOVE	DRAWING NUMBER	3-H				
SIZE	A4	SCALE	NONE	UNIT	mm	REV	A

UNLESS OTHERWISE SPECIFIED TOLERANCE	SEE ABOVE	APPROVED	張玉芬
--------------------------------------	-----------	----------	-----