

## 3mm LEDs

Order code	Manufacturer code	Description
55-0095	L-7104ED	MINIATURE 3MM AMBER LED (RC)
55-0097	L-7104ND	MINIATURE 3MM PURE ORANGE LED (RC)
55-0105	L-7104GD	MINIATURE 3MM GREEN LED (RC)
55-0107	L-7104PGD	MINIATURE 3MM PURE GREEN LED (RC)
55-0110	L-7104YD	MINIATURE 3MM YELLOW LED (RC)
55-0150	L-7104ID	3MM HIGH INTENSITY RED LED (RC)
56-0550	L-7104IT	3MM TRANSPARENT RED LED (RC)
56-0555	L-7104GT	3MM TRANSPARENT GREEN LED (RC)
56-0560	L-7104YT	3MM TRANSPARENT YELLOW LED (RC)
56-0570	L-7104EC	3MM CLEAR RED LED (RC)
56-0575	L-7104GC	3MM CLEAR GREEN LED (RC)
56-0580	L-7104YC	3MM CLEAR YELLOW LED (RC)

3mm LEDs	Page 1 of 6
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

# Kingbright®

## T-1 (3mm) SOLID STATE LAMPS

L-934H BRIGHT RED	L-934E ORANGE
L-934I HIGH EFFICIENCY RED	L-934G GREEN
L-934N PURE ORANGE	L-934Y YELLOW
L-934PG PURE GREEN	

### Features

- HIGH INTENSITY.
- LOW POWER CONSUMPTION.
- POPULAR T-1 DIAMETER PACKAGE.
- GENERAL PURPOSE LEADS.
- RELIABLE AND RUGGED.
- AVAILABLE ON TAPE AND REEL.
- DIFFUSED, TRANSPARENT AND WATER CLEAR TYPE.

### Description

The Bright Red source color devices are made with Gallium Phosphide Red Light Emitting Diode.

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.


The High Efficiency Red and Orange source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

The Pure Orange source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Pure Orange Light Emitting Diode.

The Pure Green source color devices are made with Gallium Phosphide Pure Green Light Emitting Diode.

### Package Dimensions



1 ANODE  
2 CATHODE

- Notes:
1. All dimensions are in millimeters (inches).
  2. Tolerance is  $\pm 0.25(0.01)$  unless otherwise noted.
  3. Lead spacing is measured where the lead emerge package.
  4. Specifications are subjected to change without notice.

### Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @ 10 mA		Viewing Angle
			Min.	Max.	2 $\theta$ 1/2
L-934HD	BRIGHT RED (GaP)	RED DIFFUSED	1.3	5	60°
L-934ID	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	8	50	60°
L-934IT		RED TRANSPARENT	20	125	50°
L-934EC		WATER CLEAR	20	125	50°
L-934ED	ORANGE (GaAsP/GaP)	ORANGE DIFFUSED	8	50	60°
L-934GD	GREEN (GaP)	GREEN DIFFUSED	8	32	60°
L-934GT		GREEN TRANSPARENT	20	80	50°
L-934GC		WATER CLEAR	20	80	50°
L-934YD	YELLOW (GaAsP/GaP)	YELLOW DIFFUSED	8	32	60°
L-934YT		YELLOW TRANSPARENT	10	50	50°
L-934YC		WATER CLEAR	10	50	50°
L-934ND	PURE ORANGE	ORANGE DIFFUSED	8	50	60°
L-934NT		ORANGE TRANSPARENT	20	125	50°
L-934NC		WATER CLEAR	20	125	50°
L-934PGD	PURE GREEN (GaP)	GREEN DIFFUSED	2	8	60°
L-934PGT		GREEN TRANSPARENT	3.2	20	50°
L-934PGC		WATER CLEAR	3.2	20	50°

Note:  
1.  $\theta$ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Electrical / Optical Characteristics at T<sub>A</sub>=25°C

Symbol	Parameter	Device	Typ.	Max.	Units	Test Conditions
$\lambda_{\text{peak}}$	Peak Wavelength	Bright Red High Efficiency Red Orange Green Yellow Pure Orange Pure Green	700 625 625 565 590 610 555		nm	IF=20mA
$\Delta\lambda_{1/2}$	Spectral Line Halfwidth	Bright Red High Efficiency Red Orange Green Yellow Pure Orange Pure Green	45 45 45 30 35 35 30		nm	IF=20mA
C	Capacitance	Bright Red High Efficiency Red Orange Green Yellow Pure Orange Pure Green	40 12 12 45 10 15 45		pF	VF=0V;f=1MHz
V <sub>F</sub>	Forward Voltage	Bright Red High Efficiency Red Orange Green Yellow Pure Orange Pure Green	2.0 2.0 2.0 2.2 2.1 2.0 2.25	2.5 2.5 2.5 2.5 2.5 2.6 2.6	V	IF=20mA
I <sub>R</sub>	Reverse Current	All	10		uA	VR = 5V


Absolute Maximum Ratings at T<sub>A</sub>=25°C

Parameter	Bright Red	High Efficiency Red	Green	Yellow	Pure Orange	Pure Green	Units
Power dissipation	120	105	105	105	105	105	mW
DC Forward Current	25	30	25	30	30	25	mA
Peak Forward Current [1]	150	150	150	150	150	150	mA
Reverse Voltage	5	5	5	5	5	5	V
Operating/Storage Temperature	-40 °C To +85 °C						
Lead Soldering Temperature [2]	260 °C For 5 Seconds						


Notes:  
 1. 1/10 Duty Cycle, 0.1ms Pulse Width.  
 2. 4mm below package base.




### Bright Red L-934HD




FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE




LUMINOUS INTENSITY Vs. FORWARD CURRENT




SPATIAL DISTRIBUTION


### High Efficiency Red L-934ID,L-934IT,L-934EC Orange L-934ED




FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE




LUMINOUS INTENSITY Vs. FORWARD CURRENT




SPATIAL DISTRIBUTION


Green L-934GD,L-934GT,L-934GC




FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE




LUMINOUS INTENSITY Vs. FORWARD CURRENT




SPATIAL DISTRIBUTION


Yellow L-934YD,L-934YT,L-934YC




FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE




LUMINOUS INTENSITY Vs. FORWARD CURRENT




SPATIAL DISTRIBUTION


Pure Orange L-934ND,L-934NT,L-934NC




FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE




LUMINOUS INTENSITY Vs. FORWARD CURRENT




SPATIAL DISTRIBUTION


Pure Green L-934PGD,L-934PGT,L-934PGC




FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE



LUMINOUS INTENSITY Vs. FORWARD CURRENT



SPATIAL DISTRIBUTION