

CONTROL PRODUCTS

Heavy Duty Footswitch

- Industrial die-cast footswitch
- Heavy duty applications
- Snap action and slow action contact blocks
- Self-rising saddle-washer terminal connections
- Single or double double-pole contact blocks
- Positive opening operation
- Silver contacts
- Anti Slip foot pedal
- Non-slip rubber feet



PART NO.	DESCRIPTION
CFSHC1	Guarded 1 snap action contact block
CFSHC2	Guarded 1 slow action contact block
CFSHC1C1	Guarded 2 snap action contact blocks
CFSHC2C2	Guarded 2 slow action contact blocks
CFSHC1C2	Guarded 1snap and 1 slow action contact blocks

SPECIFICATIONS

Thermal current (Ith)Rated	10A
insulation voltage (Ui)	500VAC 600VDC
Protection against short circuits	fuse 10A 500V type aM

Alternate current: AC15 (50-60Hz)

Ui (V)	250	400	500
Ie (A)	6	4	1
Direct current: DC13			
Ue (V)	24	125	250
Ie (A)	6	1.1	0.4

Connectors flexible wire sizes	min	1 x 0.5 mm ² (1 x AWG 20)
	max	2 x 2.5mm ² (2 x AWG 14)

Actuating force	single snap action	10N
	single slow action	12N
	double snap action	13N
	double slow action	15N

Ambient temperature	from -25°C to +80°C
Weight guarded	-1.4 kg

